## **Sanitary**



### Diaphragm Seals



The Trerice Sanitary Diaphragm
Seal is intended for use in the food
and pharmaceutical industries, or in any
application where a thorough cleaning
of the wetted surface is required.
Ease of maintenance is ensured as
surfaces that contact the process media
are virtually free of crevices. The all
welded construction and external
Tri-Clamp connection allow for easy
removal and cleaning.

Selection of the proper diaphragm seal is the sole responsibility of the user. Temperature and pressure limitations must be considered. Please refer to the Diaphragm Seal Design & Operation Section of this catalog. Improper application may cause failure of the seal, resulting in possible personal injury or property damage.

For correct use and application of all diaphragm seals, please refer to Diaphragm Seal Standard ASME B40.2.

| SPECIFICATIONS |                               |                   |                       |                     |                                |
|----------------|-------------------------------|-------------------|-----------------------|---------------------|--------------------------------|
| Style          | Available<br>Diaphragm Types* | Diaphragm<br>Size | Process<br>Connection | Clean-out<br>Design | 1/4 NPT<br>Flushing Connection |
| 472            | Type W                        | Sanitary          | Tri-Clamp             | Yes                 | No                             |

<sup>\*</sup> W = Welded Metal

Note: Due to the variety of available diaphragm seal configurations and materials, it is not possible to list each weight in this catalog. Please consult factory.

Sample Order Number: W 4 72 09 S S S

### **HOW TO ORDER**

| Diaphragm<br>Type | Diaphragm<br>Size | Style        | Connection<br>Size                           | Diaphragm<br>Material    | Process<br>Housing<br>Material | Instrument<br>Housing Material |
|-------------------|-------------------|--------------|--|--------------------------|--------------------------------|--------------------------------|
| W Welded          | 4 Sanitary        | 72 Tri-Clamp | See<br>Connection<br>Sizes on<br>Sizes Table | S 316 Stainless<br>Steel | S 316 Stainless<br>Steel       | S 316 Stainless Steel          |






# Sanitary

All dimensions are nominal. Dimensions in [ ] are in millimeters.

## **Diaphragm Seals**



| Tri-Clamp Size | A                         | Н         | D         |
|----------------|---------------------------|-----------|-----------|
| 11/2"          | 1/4, 1/2 NPT as specified | 1.81 [46] | 2.00 [50] |
| 2"             | 1/4, 1/2 NPT as specified | 1.38 [35] | 2.50 [64] |

#### **Sizes**

| Connection Sizes |                                |                       |  |  |
|------------------|--------------------------------|-----------------------|--|--|
| Code             | Instrument<br>Connection (NPT) | Process<br>Connection |  |  |
| 07               | 1/4                            | 11/2" Tri-Clamp       |  |  |
| 08               | 1/2                            | 11/2" Tri-Clamp       |  |  |
| 09               | 1/4                            | 2" Tri-Clamp          |  |  |
| 10               | 1/2                            | 2" Tri-Clamp          |  |  |

Clamps, gaskets and ferrules are not supplied by Trerice.

Master Gauge Go.